3 ¹ / ₈ "	80mm –				– 80mm	3 ¹ / ₈ "
0 78	Commi				0011111	3 78
2 ³ / ₄ "	70mm –				– 70mm	2 ³ / ₄ "
2 ³ / ₈ "	60mm				– 60mm	2 ³ / ₈ "
2 /8	60mm –				- 60111111	Z 18
2"	50mm -				– 50mm	2"
1 ⁵ / ₈ "	40mm				40mm	1 ⁵ / ₈ "
1 /8	40mm –				– 40mm	1 /8
1 ¹ / ₈ "	30mm -		Focus on the centre of the thick black line in the box below from an		– 30mm	1 ¹ / ₈ "
			angle of 45 degrees.			
3/4"	20mm -				– 20mm	³ / ₄ "
⁹ / ₁₆ "	14mm -	-			– 14mm	⁹ / ₁₆ "
³ / ₈ "	10mm -				_ 10mm	³ / ₈ "
¹⁵ / ₆₄ "	6mm -				– 6mm	¹⁵ / ₆₄ "
⁵ / ₆₄ "	2mm -	-			– 2mm	⁵ / ₆₄ "
This text should be perfectly in focus		focus	Focus here	This	text should be perf	ectly in focus
⁵ / ₆₄ "	2mm -				– 2mm	⁵ / ₆₄ "
¹⁵ / ₆₄ "	6mm -				– 6mm	¹⁵ / ₆₄ "
³ / ₈ "	10mm -				– 10mm	³ / ₈ "
⁹ / ₁₆ "	14mm –				– 14mm	⁹ / ₁₆ "
³ / ₄ "	20mm –				– 20mm	³ / ₄ "
			Focus test chart V2.00			
1 ¹ / ₈ "	30mm -		Copyright Tim Jackson 2004 tim@FocusTestChart.com http://FocusTestChart.com		– 30mm	1 ¹ / ₈ "
			nttp://rocustestenart.com			
1 ⁵ / ₈ "	40mm –				– 40mm	1 ⁵ / ₈ "
2"	50mm –				– 50mm	2"
2 ³ / ₈ "	60mm -				– 60mm	2 ³ / ₈ "
2 ³ / ₄ "	70mm –				– 70mm	2 ³ / ₄ "
	2					· -
3 ¹ / ₈ "	80mm –				– 80mm	3 ¹ / ₈ "